UNIT CONDENSER			EVADCO	EVAPCO, INC. Evaped		DWG. # CEWRTM2406-DRA-ST		-
MODEL#	PMRC-735	SCALE NTS	EVAPC	J, IIIC.	Si	ERIAL #	DATE:	11/27/2025
2. MPT DENOT FPT DENOT BFW DENOT BFW DENOT FLG DENOT PE DENOTE ACCESSOR 4. 3/4" [19mm] RECOMMES 50 psi [344 k 6. DIMENSION ENGLISH F [METRIC] [17. * - APPROXI	S PLAIN END HT DOES NOT INCLUDE IES (SEE ACCESSORY DRAWIN DIA. MOUNTING HOLES. REFEE IDED STEEL SUPPORT DRAWIN ATER PRESSURE 20 psi [137 kF Pa] MAX. S LISTED AS FOLLOWS: T-IN	R TÓ NG. Pa] MIN,		FACE B LAN VIEW		CE C		FACE D
					<u>. As</u>	<u> </u>		
	2'-6 3/8" * [772]	4'-9" * [1448]						
		O [100] PE O [100] PE	1'-10 1/4" [565] *	5'-1 1/8" [1553]				
2"[50] N MAKE 3" 2'-5"[737]	UP [80] MPT DRAIN		13'-7 1/2" [4153] 9'-11" [3023] *	8'-6 3/8" [2600]				
1'-8" [50a 3 7	8] 4 3/4" [121] 5 1/8" [98] 3'-10 1/2" [1181]	3"[80] OVEF] MPT RFLOW	1'-7 1/8" [486]	24'-0 7 [7337	⁷ /8"	-	1'-6" [457]
	[1101]	9'-9 3/4" [2991] FACE B			FACI	≣ A		
SHIPPING WEIGHT	26410 lbs+ [11980] kç		ATING 34180 lbs+ [15505] kg+	HEAVIEST SECTION WEIGHT	9830 lbs+ [4460] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY:	JLG