NIT CONDENSER			DWG.#	REV
CONDENSER IODEL# SCALE		EVAPCO, INC. Evapeo	CEWRTM2414-DRA-ST	DATE:
PMRC-1056	NTS		GENIAL #	11/25/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH F-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.		FACE B PLAN VIEW	FACE A	FACE D
	4'-9" *			
O (4) 4* [100] PE	O	3'-11 3/4" [1213] * 7'-2 5/8" [2200]		
OVERSIZED ACCESS DOORS 2"[50] MPT MAKE UP 3"[80] MPT DRAIN 2'-5"[737]		9'-11" [3023] * 8'-6 3/8" [2600]		
	3"[80] MPT OVERFLOW	1'-7 1/8" [486]	24'-0 7/8" [7337]	1'-6" [457]
[2991] FACE B				
SHIPPING 43880 lbs+ [19905] kg+	OPERATING WEIGHT	52270 lbs+ [23710] kg+ HEAVIEST SECTION 16720 lbs+ [7585] kg+	NO. OF SHIPPING SECTIONS	DRAWN BY: JLG