INIT	CONDENSER			EVAPCO, INC.			DWG. # CEWRTM1208-DRA-ST	REV -
IODEL#	PMRC-431	SCALE NT	s	EVAPC	O, INC		SERIAL#	DATE: 11/27/2025
2. MPT DENOT FPT DENOT FPT DENOT BFW DENOT GVD DENOT FLG DENOT FLG DENOT ACCESSOR! 4. 3/4" [19mm RECOMME. 5. MAKE-UP W 50 psi [344 6. DIMENSION ENGLISH [METRIC] 7. * - APPROX	IS PLAIN END IGHT DOES NOT INCLUDE IES (SEE ACCESSORY DRAWINGS). I) DIA. MOUNTING HOLES. REFER T IDED STEEL SUPPORT DRAWING. VATER PRESSURE 20 psi [137 kPa] N kPa] MAX. IS LISTED AS FOLLOWS: ET-IN	4IN,				<u>FACE B</u> <u>PLAN VIEW</u>	FACE A	FACE D
2"[50] N MAKE 3"[. 2'-5"[737] 1'-8" [508]	UP ————————————————————————————————————		A48] O REFRIG IN REFRIG OUT	2'-6 3/4" [781] * 14'-4" [9'-11" [3023] *	4369]	5'-9 5/8" [176 8'-6 3/8" [260		
1'-8" [508]	3 7/8" [98]—5 1/8" [130]		3"[80] MPT OVERFLOW			1'-7 1/8" [486	3]	

FACE A FACE A

 SHIPPING WEIGHT
 15890 lbs+ [7210] kg+
 OPERATING WEIGHT
 19680 lbs+ [8930] kg+

9'-9 3/4<u>"</u> [2991]

4 3/4" [121] 3'-10 1/2" [1181]

> HEAVIEST SECTION WEIGHT

10560 lbs+ [4790] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG