

UNIT	CONDENSER
MODEL #	eco-PMRC-1225


EVAPCO, INC. 

DWG. #	CEWRTM3610-DRA-ST
SERIAL #	DATE: 2/19/2026

NOTES:


- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE B

PLAN VIEW



FACE A



FACE A

SHIPPING
WEIGHT

61610 lbs+ [27950] kg+

OPERATING
WEIGHT

73900 lbs+ [33525] kg+

HEAVIEST SECTION
WEIGHT

23900 lbs+ [10845] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**