

UNIT	CONDENSER
MODEL #	eco-PMRC-1256

EVAPCO, INC.



DWG. # CEWRTM3612-DRA-ST

REV -


SERIAL #

DATE: 2/19/2026

NOTES:



- (M)- FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE B

PLAN VIEW



FACE A



FACE A

SHIPPING
WEIGHT

69990 lbs+ [31750] kg+

OPERATING
WEIGHT

82510 lbs+ [37430] kg+

HEAVIEST SECTION
WEIGHT

28090 lbs+ [12745] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: JLG