

UNIT	CONDENSER
MODEL #	eco-PMRC-558


DWG. #	CEWR121210-DRA-ST	REV	-
SERIAL #		DATE:	2/20/2026

NOTES:

- (M) - FAN MOTOR LOCATION.
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
- DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
- * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING.

Preliminary


FACE B



FACE B
PLAN VIEW

FACE C

FACE D



FACE A