

UNIT	CONDENSER
MODEL #	eco-PMRC-558


EVAPCO, INC. 

DWG. #	CEWR121210-DRA-ST	REV	-
SERIAL #		DATE:	2/20/2026

NOTES:


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

Preliminary




FACE B

FACE B
PLAN VIEW



FACE C

FACE D



FACE A

SHIPPING
WEIGHT

25040 lbs+ [11360] kg+

OPERATING
WEIGHT

29920 lbs+ [13575] kg+

HEAVIEST SECTION
WEIGHT

19290 lbs+ [8750] kg+

NO. OF SHIPPING SECTIONS

2

DRAWN BY: **JLG**