

| | | |
|---------|--------------|-----------|
| UNIT | CONDENSER | |
| MODEL # | eco-PMRC-829 | SCALE NTS |


EVAPCO, INC.




| | | | |
|----------|-------------------|-------|-----------|
| DWG. # | CEWR121806-DRA-ST | REV | - |
| SERIAL # | | DATE: | 2/19/2026 |

NOTES:

1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN,
50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT
USE FOR PRE-FABRICATION OF CONNECTING PIPING



FACE B



FACE A

SHIPPING WEIGHT 27950 lbs+ [12680] kg+ OPERATING WEIGHT 34750 lbs+ [15765] kg+ HEAVIEST SECTION WEIGHT 19170 lbs+ [8700] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG