JNIT COMPENSED				(6)	DWG.#	REV
CONDENSER		EVAPCO, 3	INC E	/apco	CEWR122012-DRA-ST	- DATE:
eco-PMRC-1095 SCALE N	TS	LVAI CO/ .			SERIAL#	12/14/2025
NOTES: 1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.			FACE B PLAN VIEW		FACE A	FACE D
3'-0 7/8" * 5'-8 [937] [1	5/8" * 743]		1)3			
O (2) 4* [100] PE	O	3'-11 3/4" [1213] *	7'-2 5/8" [2200]			
OVERSIZED ACCESS DOORS 2"[50] MPT 5 1/8" [130] MAKE UP 3"[80] MPT DRAIN 2'-5"[737]	O REFRIG OUT	15'-9" [4801] 9'-11" [3023] *	8'-6 3/8" [2600]			
1'-8" [508] 3 7/8" [98] 	10 3/8" 616]	3"[80] MPT OVERFLOW	2'-3 1/4" [692]—		20'-0 1/4" [6102]	
<u>FA</u>				FACE A		
SHIPPING WEIGHT 47100 lbs+ [21365] kg+	OPERATING WEIGHT	55340 lbs+ [25105] kg+	HEAVIEST SECTION WEIGHT	37530 lbs+ [17025] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: JLG