

UNIT	CONDENSER
MODEL #	eco-PMRC-1916

EVAPCO, INC.




DWG. # CEWR124008-DRA-ST

REV -
SERIAL #
DATE: 2/20/2026

NOTES:


1. (M)- FAN MOTOR LOCATION.
2. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS).
4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX.
6. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
[METRIC] [mm]
7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.

FACE C




FACE B
PLAN VIEW

FACE A



FACE B



FACE A

SHIPPING
WEIGHT

70240 lbs+ [31865] kg+

OPERATING
WEIGHT

86320 lbs+ [39155] kg+

HEAVIEST SECTION
WEIGHT

26460 lbs+ [12005] kg+

NO. OF SHIPPING SECTIONS

3

DRAWN BY: **JLG**