ONDENSER				DWG.# CEWR124004-DRA-ST -	
MODEL#	SCALE NTS	<b>EVAPC</b> (	O, INC. Evapeo	SERIAL#	DATE: 40/45/0005
eco-PMRC-1148	NIS				12/15/2025
1. (M)- FAN MOTOR LOCATION. 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS). 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 5. MAKE-UP WATER PRESSURE 20 psi [137 kPa] MIN 50 psi [344 kPa] MAX. 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] [mm] 7. * - APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIR	N,	FACE B PLAN VIEW	FACE		FACE D
3'-0 7/8" * 5'-8 5/8' [937]	REPRIGOUT  9'	12'-11" [3937] -11" [3023] * 8'-6 3/8" [2600]  2'-3 1/4" [692]  OVERFLOW	40	(M)	2'-5 1/8" [740]

HEAVIEST SECTION WEIGHT FACE A

16050 lbs+ [7285] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

JLG

FACE B

46470 lbs+ [21080] kg+

OPERATING WEIGHT

61910 lbs+ [28085] kg+

SHIPPING WEIGHT