

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

MODEL #	U-EJETME2-2143H0100F1KA
---------	-------------------------

DWG. # UEJETM2-SE-16,18

DATE	9/16/2025
------	-----------



Technical drawing of a mechanical part, likely a bracket or support, showing dimensions and labels.

Dimensions (in inches):

- Overall width: $45 \frac{3}{8}$
- Distance from left edge to center of hole: $* 41 \frac{3}{8}$
- Distance from right edge to center of hole: $3 \frac{1}{4}$
- Distance from center of hole to right edge of flange: $4 \frac{7}{8}$
- Distance from center of hole to right edge of base: $7 \frac{1}{4}$ (labeled **)
- Overall height: $60 \frac{3}{4}$
- Distance from left edge to center of hole: 55
- Distance from left edge to right edge of base: $57 \frac{1}{2}$
- Distance from right edge of base to right edge of flange: $1 \frac{1}{4}$

Labels:

- AIR
- LOW

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.

2" MPT
DRAIN

ROOM

SHIPPING
WEIGHT

950 lbs+ [435] kg+

OPERATING WEIGHT	10,000
------------------	--------

1030 lbs+ [470] kg+