

This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.

CUSTOMER

MODEL #

U-EJETME3-3266F0100F1KA

SCALE


N.T.S.

DWG. #

UEJETM3-SE-16,18

REV. 0


DATE	9/27/2025
------	-----------



– NEMA 4X
JUNCTION BOX

NOTES:

- 1) * = HANGER HOLE LOCATION.
- 2) RIGHT HAND MODEL SHOWN.
- 3) HANGER HOLES ARE FOR 3/4 INCH THREADED ROD.
- 4) WATER DEFROST ADDS 1 3/4" INCHES TO HEIGHT OF STANDARD UNIT AND CHANGES DRAIN SIZE.
- 5) ALL DIMENSIONS ARE FOR REFERENCE AND SHOULD NOT BE USED FOR PREFABRICATION OF PIPING OR SUPPORTS.
- 6) **= HEIGHT OF SUCTION HEADER AND INSTALLED THERMOWELL FITTING ABOVE CABINET. CUSTOMER IS RESPONSIBLE TO ACCOUNT FOR ADDITIONAL HEIGHT NECESSARY FOR RTD AND ACCESS.



Technical drawing of a vertical riser assembly. The drawing shows a cross-section of the assembly with various dimensions and labels. The top dimension is 45 3/8. Below it, the distance from the centerline to the edge is 41 3/8, with a 3/4 offset on each side. The total height of the riser is 57 1/2. The distance from the top of the riser to the top of the drain is 62 3/4. The distance from the centerline to the edge of the drain is 55, with a 1 1/4 offset on each side. The total width of the assembly is 57 1/2. The drawing also shows a 2" MPT drain and an air flow indicator.

Labels and dimensions:

- 45 3/8
- 3/4
- * 41 3/8
- 3/4
- 4 7/8
- ** 9 1/4
- 57 1/2
- 62 3/4
- 2" MPT DRAIN
- AIR FLOW
- 1 1/4
- 55
- 57 1/2

PROJECT

ROOM

SHIPPING
WEIGHT

1520 lbs+ [690] kg+

OPERATING WEIGHT	10000
------------------	-------

1810 lbs+ [825] kg+