



Since 1976  
An Employee-Owned Company



# GLOBAL PRODUCT CATALOG

FULL SPECTRUM GLOBAL SOLUTIONS

Commercial HVAC | Industrial Refrigeration | Power Generation | Industrial Process

## EVAPCO for LIFE

EVAPCO is more than a name. We are the global innovator in heat transfer solutions for the Commercial HVAC, Industrial Refrigeration, Power and Industrial Process markets. We pledge to make everyday life easier, more comfortable, more reliable and more sustainable for people everywhere.

## OUR COMMITMENT

We never stop innovating. We set out to find groundbreaking solutions that transform the way the world works for the better. It's why we have more than 300 active patents worldwide. We also guarantee performance and put every solution through rigorous research and testing to ensure maximum efficiency and reliability.

## PROTECTING THE ENVIRONMENT

Innovation and environmental sustainability go hand-in-hand at EVAPCO. Our industrial heat transfer equipment not only conserves natural resources and helps reduce noise pollution, but also features recycled steel content in construction. Our stainless steel units are constructed of panels that contain up to 65% of recycled content and our galvanized units contain over 79%\*. From sound reduction to water conservation to chemical elimination, we are developing new technologies that deliver ultimate operating advantages to our clients while protecting the planet for every generation to come.

\*Applicable to US manufactured product.





## INSIDE

Who We Are . . . . .	2
Table of Contents . . . . .	3
Welcome . . . . .	4
Full Spectrum Global Solutions . . . . .	5
Closed Circuit Coolers . . . . .	6
Cooling Towers . . . . .	8
Condensers & Gas Coolers . . . . .	10
Evaporators . . . . .	12
Hygienic Air Handling Units . . . . .	14
Evapcold . . . . .	15
EVAPCO LMP . . . . .	16
EVAPCO Select Tech. . . . .	17
RVS ASME Pressure Vessels . . . . .	18
Water Treatment Systems . . . . .	19
EVAPCO Power . . . . .	20
EvapTech . . . . .	20
EVAPCO Dry Cooling . . . . .	21
EVAPCO Air Solutions . . . . .	22
Thermal Ice Storage Systems . . . . .	23
EVAPCO Alcoil . . . . .	24
Replacement Parts . . . . .	25
Mr. GoodTower Service Centers . . . . .	25
Tower Components, Inc. . . . .	26
Fiberglass Pultrusions . . . . .	26
FanTR . . . . .	27
North America Manufacturing Plants . . . . .	28
International Manufacturing Plants . . . . .	29
International Manufacturing Plants . . . . .	30



## Welcome to EVAPCO...

We are pleased to offer a full spectrum of heat transfer product solutions from 100 percent evaporative to 100 percent dry. These products are available in a wide range of sizes from the smallest factory assembled units to the largest field-erected products ... all available on a worldwide basis. We are quite proud of our full spectrum of global product solutions!

As a respected leader in evaporative cooling technologies, our commitment to Research and Development has led to innovative solutions for our constantly changing world. Solutions that are energy efficient, conserve water, and comply with local regulations.

But that isn't only what makes EVAPCO stand out above the rest. What sets EVAPCO apart from other manufacturers in the Commercial HVAC, Industrial Refrigeration, Power Generation and Industrial Process markets all points back to our team, the EVAPCO family, of which you are a vital part.

EVAPCO associates are fiercely loyal to each other, to our representatives and, most importantly, to the people they serve. We recognize that our customers are at the center of our success and we never take for granted the level of trust that you put in us when it comes to your heat transfer needs.

We demand excellence in everything that we do and we are committed to delivering the highest quality services and products. We're here to make your job easier, to be your partner, and to exceed your expectations.

EVAPCO for Life sums up our commitment. It is our promise that we will always provide you with the most innovative and most reliable products, created and built by the best people in the industry. By choosing EVAPCO, you're letting us know that we're doing the best job possible for you.

We thank you, not only for your business, but for inspiring our message. By working together with you, EVAPCO has been able to consistently breed a level of innovation, craftsmanship, and professionalism that our competitors find difficult to match! We couldn't do it without you!

Very sincerely yours,

A handwritten signature in black ink that reads "William G. Bartley". The signature is fluid and cursive, with a large, sweeping flourish at the end.

William G. Bartley  
Chairman and CEO

# FULL SPECTRUM GLOBAL SOLUTIONS



EVAPCO provides a full spectrum of global product solutions for the Commercial HVAC, Industrial Refrigeration, Power Generation and Industrial Process markets.

From the smallest factory assembled cooling tower to the largest field erected air-cooled steam condenser, we offer heat transfer products designed to meet the water and energy requirements for any project. We are committed to providing solutions that are energy efficient and conserve water.

Our latest heat transfer solutions are the factory-assembled eco-Air Series of Dry Coolers, Air Cooled Condensers and Adiabatic Coolers and Condensers. The eco-Air Series completes our successful eco-family of closed circuit coolers and condensers with water-saving dry and adiabatic technology.

As an industry leader in third-party performance certifications, our fully-rated products enable you to operate your cooling systems efficiently and with complete peace of mind.



EVAPCO Air Solutions V Series, Germany

# CLOSED CIRCUIT COOLERS

## Dry & Adiabatic

Available in a wide range of footprints, motor types, control options and capacities, this complete line of Air Cooled/Dry & Adiabatic products offers maximum water savings, reduced maintenance, and simplified operation.



**eco-Air Flat Dry Cooler**  
Flat Air Cooled Fluid Cooler



**eco-Air V Dry Cooler**  
Air Cooled V Fluid Cooler



**eco-Air V Adiabatic Cooler**  
Air Cooled V Fluid Cooler with Adiabatic Pads



**eco-Air V Spray Cooler**  
Air Cooled V Fluid Cooler with Adiabatic Spray System



**eco-Air Double Stack Dry Cooler**  
Air Cooled High Capacity Fluid Cooler



**eco-Air Double Stack Adiabatic Cooler**  
Air Cooled High Capacity Fluid Cooler with Adiabatic Pads

## Factory Assembled Induced Draft

Closed Circuit Coolers provide incredible cooling efficiency. Easier to maintain than open system cooling towers, EVAPCO's closed circuit coolers are an excellent option for any cooling system.



**eco-ATWB**  
Water-Conserving Advanced Technology with Increased Dry Cooling Capacity



**eco-ATWB-H**  
Hybrid Cooler Providing a Combination of Water & Energy Savings with the Highest Dry Bulb Switch Point



**ESW4**  
Ideal for wet cooling applications where thermal and energy efficiency is of utmost concern.



**ATWB**  
The original Advanced Technology provides an induced-draft, axial fan solution for a wide array of cooling applications. Also available in 7' wide containerized boxes.



**PHW**  
The PHW offers more selections for large projects: more capacity with a smaller plan area, fewer motors, and less weight. More equipment choices, and more design flexibility mean greater value for the end user.

## Factory Assembled Forced Draft

The LSWE and LRWB are the industry standard in low-sound, centrifugal fan, forced-draft closed circuit coolers.



**eco-LSWE**

Low Sound  
Water Conserving  
Centrifugal Fan  
Increased Dry Cooling Capacity



**LRWB**

Low Profile | Low Sound  
Centrifugal Fan

These water saving eco-units offer improved dry operation on projects with indoor/ducted or confined layouts and low sound requirements.



**LSWE**

Low Sound  
Centrifugal Fan



**eco-LRWB**

Low Profile | Low Sound  
Water Conserving  
Centrifugal Fan  
Increased Dry Cooling Capacity



ATWB Closed Circuit Cooler with optional Smart Shield Water Treatment System


# COOLING TOWERS



AT Cooling Tower with optional features

## Factory Assembled Induced Draft

EVAPCO's state-of-the-art induced draft cooling technology delivers superior operating advantages in any climate. From performance to maintenance, these solutions simply work harder. Choose from counterflow cooling towers, or crossflow and solar-powered options.



**AT**  
Counterflow Cooling Towers



**AXS**  
Crossflow Cooling Towers




**SUN**  
Solar Powered Cooling Towers

## Factory Assembled Forced Draft

These centrifugal fan cooling towers are utilized in low noise, high static, or ducted applications and are a good solution for tight enclosures.



**LSTE**  
Low Sound Centrifugal Fan



**LPT**  
Low Profile | Low Sound Centrifugal Fan

## Modular Induced Draft

Designed in large modules for ease of installation and reduced field assembly, the AT Atlas is the most energy efficient modular cooling tower on the market.



**AT ATLAS**  
Modular Induced Draft Counterflow



AT Atlas installation

# CONDENSERS & GAS COOLERS

## Dry & Adiabatic

Available in a wide range of footprints, motor types, control options and capacities, this complete line of Air Cooled/Dry & Adiabatic products offers unparalleled flexibility.



**eco-Air Flat Series**  
Air Cooled Condenser  
Or Gas Cooler



**eco-Air V Series**  
Air Cooled Condenser  
Or Gas Cooler



**eco-Air Adiabatic Series**  
V Series Air Cooled Condenser  
Or Gas Cooler with Adiabatic Pads




**eco-Air Spray Series**  
V Series Air Cooled Condenser with  
Adiabatic Spray System

## Factory Assembled Induced Draft

EVAPCO condensers are equipped with low pressure drop and high capacity Thermal-Pak® II Coil design. The patented Ellipti-fin® coil technology further enhances our industry leading performance while saving on water consumption.



**ATC-E**  
Advanced  
Technology Series



**eco-ATC-A**  
Water Conserving  
Advanced Technology



**eco-ATC-H**  
Optimum Wet/Dry  
Hybrid Technology



**PHC-E**  
Great for large industrial refrigeration  
projects, the PHC offers layout flexibility  
and reduced piping.



ATC-E Evaporative Condensers with optional external service platform

## Factory Assembled Forced Draft

EVAPCO's forced draft product evaporative condenser lines are equipped with owner-oriented features and benefits for easier installation, maintenance, and operation! Multiple axial fans located at grade in the PMC-E offer redundancy and improved drive accessibility. While providing similar drive accessibility, the centrifugal fans in the LSC-E and LRC are suited for low noise or ducted applications.



**PMRC**

Low Power Axial Fan



**LSC-E**

Low Sound Centrifugal Fan



**LRC**

Low Profile | Low Sound  
Centrifugal Fan



**eco-PMRC**

Water Conserving Low Power  
Axial Fan

The same features and benefits of the PMRC line but utilizing patented Ellipti-fin® coil technology to offer water savings benefits.



PMC-E Evaporative Condenser with optional external service platform



SSTME Evaporator with long-throw adapter

## Ceiling Hung Solutions

Enjoy industrial, low maintenance and easy-to-clean cooling in your food storage and processing facilities with EVAPCO's Superior Stainless Technology E-series evaporators, the only independently certified thermal performance and power rated offering available today.



**SSTME**  
Medium Capacity  
Unit Coolers



**SSTHE**  
Reduced Charge Medium to  
Large Hybrid Product Cooler



**SSTLE**  
Large Capacity  
Product Coolers



**SSTXE**  
Low Profile  
Unit Coolers



**SSTWE\***  
Low Velocity Hygienic  
Workroom Units



**SSTDE\***  
Dual Coil Low Profile  
Unit Coolers



**EJETHE**  
Medium to Large Capacity  
Unit Coolers



**EJETME**  
Small to Medium Capacity  
Unit Coolers



**EJETXE**  
Low Profile Unit Coolers

\*These models fall outside the scope of the AHRI Unit Coolers Certification Program but are rated in accordance with AHRI Standard 420.

## Ultra Hygienic Ceiling Hung Solutions

Ultra Series Industrial Evaporators offer additional design features and accessibility for cleaning beyond those available in the standard SSTME and SSTWE product lines, making them the most hygienic ceiling-hung evaporators in the market.



**U-SSTME**  
Medium Capacity  
Hygienic Unit Coolers



**U-SSTWE\***  
Low Velocity Hygienic  
Workroom Units




**U-EJETME**  
Small to Medium Capacity  
Hygienic Unit Coolers

\*This model falls outside the scope of the AHRI Unit Coolers Certification Program but are rated in accordance with AHRI Standard 420.

## Custom Design Capabilities


We offer a broad range of unit configurations, engineering expertise and manufacturing capability to design and build virtually any type of non-cataloged custom coil or special unit.



Draw Through Coils  
with Inlet Air Filters



Stacked Blast Freezer Evaporator



Spiral Blast Freezer Evaporator



SSTWE Work-Room Evaporators

# HYGENIC AIR HANDLING UNITS



Critical Process Air (CPA) Hygienic Air Handling System

## Hygienic Cooling & Dehumidification

Engineered to deliver conditioned, purified air to critical food preparation, production and packaging areas in your facility. Allow us to solve your hygienic air handling needs with options ranging from HEPA filtration, UV lights, fully wash down welded stainless construction, room pressurization and many more.



**CPA**

Critical Process Air Systems



**SSTP-E**

Penthouse Evaporators



**EDF**

Make-Up Air Systems




Critical Process Air (CPA) Hygienic Air Handling System


## Packaged Low Charge Ammonia Refrigeration Systems

Requiring just a fraction of the refrigerant charge as compared to traditional field-erected systems, each low charge ammonia refrigeration Evapcold system is expertly crafted as a single-source, quick-to-install solution. Units are available with many optional accessories, including dual compressors.

### Penthouses



**LCR-P-W**  
Penthouse Refrigeration System  
Water Cooled



**LCR-P-A**  
Penthouse Refrigeration System  
Adiabatic Air Cooled



**LCR-P-A**  
Penthouse Refrigeration System  
Air Cooled

### Chillers



**LCR-C-W**  
Packaged Ammonia Chiller  
Water Cooled



**LCR-C-A**  
Packaged Ammonia Chiller  
Air Cooled




**LCR-C-A**  
Packaged Ammonia Chiller  
Adiabatic Air Cooled

### Split Systems



**LCR-S-W**  
VersaSplit™ Low Charge Ammonia  
Water-Cooled Split



**LCR-S-A**  
VersaSplit™ Low Charge Ammonia  
Air-Cooled Split



**LCR-S-A**  
VersaSplit™ Low Charge Ammonia  
Adiabatic Air-Cooled Split



Evapcold Low Charge Ammonia Packaged Refrigeration System LCR-P-A



Evapcold Low Charge Ammonia Machinery Room LCR-P-W

## Packaged Transcritical CO<sub>2</sub> Refrigeration Systems

The flagship transcritical CO<sub>2</sub> Purity line uses a variety of patented technologies to maintain optimal operation while providing high reliability. The Purity systems are available in low, medium and high temperature applications, serving both the commercial retail and industrial refrigeration markets. These systems also offer an efficient, environmentally friendly, and sustainable solution for cold storage facilities of all sizes and smaller industrial applications where previously, synthetic refrigerants may have been used. All EVAPCO LMP systems are designed and manufactured with simple installation and rapid commissioning in mind.



Purity Industrial Rack



Purity Commercial Rack




Purity Rack Highlighting Microprocessor Control Panels



Purity Rack with Outdoor Enclosure Manufacturing in Process



Stainless Steel Medium Pressure Valve Groups (1160 psi / 80 bar)



Copper Low Pressure Valve Groups (650 psi / 50 bar)

## About EVAPCO SelectTech

EVAPCO SelectTech is a food plant systems integrator specializing in design-build-installation of facility systems, production line integration, process automation, ammonia refrigeration, supervisory systems, and IT integration.



### Refrigeration

Ammonia Control System Integration



### Production Line Systems

Automation/Integration



### Processing Controls

Ingredients, Batching, Cooking, Freezing



### Panel Building

UL508A Certified



### Full Turnkey Philosophy

Design, Build, Installation, Commissioning



### Facility Controls

Plant-Wide Pressurization, Critical Process Air (CPA) Handling Automation, Compressed Air Systems, Water/Wastewater Treatment Controls



RVS MPC Chiller Package

## Refrigeration Packages & ASME Pressure Vessels

Our variety of ASME pressure vessels and recirculation packages offer the latest in microprocessor technology with the Matrix II providing total control for recirculator package pumps, level control and liquid make-up for vessels and system alarms.



**MRP**

Vertical & Horizontal  
Liquid Recirculator Package



**MPC**

Semi-Welded  
Plate Chiller Package



**MVI & MVA**

Intercooler & Accumulator Package



**MTP**

Transfer Package



**Matrix II**


Microprocessor™  
Control Panel



**Custom Oil and Gas Vessels and Packages**

# WATER TREATMENT SYSTEMS

## Water Solutions



**Pulse~Pure®**  
Chemical-free,  
environmentally conscious  
water treatment systems.



**Water Saver™**  
Pretreatment system for  
evaporative cooling equipment.



**Smart Shield®**  
Reliable, sustainable, solid chemistry  
water treatment system.



**Pass-Protect®**  
Passivation enhancement  
process to minimize the  
formation of white rust.



AT Cooling Tower with optional *Pulse~Pure®* Non-Chemical Water Treatment System



Smart Shield® Factory-Mounted Water Treatment System

## EvapTech – Field Erected Cooling Towers




EvapTech Cooling Towers



**Series EC**  
Custom Counterflow




**Meridian® Series**  
Modular Counterflow (FM Approved optional)



**Series EX and Series ESX**  
Custom Crossflow and FM Approved Crossflow



Reconstruction services



**EvapDri**  
Plume abatement & water conservation



**Series ECC**  
Concrete Counterflow




**Series ECB**  
Back-to-Back Counterflow



**Series ES & ESP**  
FM Approved Counterflow



EvapTech Asia Pacific



Major projects/Natural draft refurbishments

## EVAPCO Dry Cooling – Dry Cooling Technology




### EVAPCO Dry Cooling Air Cooled Steam Condensers and Heat Exchangers



**Advanced Technology ACHE**  
Multiple ACHE Tube Bundles Positioned Beneath Large Fans



**Advanced Technology ACHE**  
Saves Plot Plan, Aux. Power, and Lowers Noise



**Advanced Technology™ ACC**  
Onsite Modularization



**Advanced Technology™ ACC**  
Onsite Modularization



**Advanced Technology™ ACC**  
Offsite Modularization



**eco-Air Air Cooled Heat Exchangers**  
Factory Assembled Packaged Units Located at Grade



**eco-Air Air Cooled Heat Exchangers**  
Easy Installation of Factory Assembled Packaged Units



**eco-Air Air Cooled Heat Exchangers**  
Factory Assembled Packaged Units Installed on Common Structure



V Series Energizers, Denmark

The EVAPCO Europe Dry Cooler Series offers unparalleled flexibility in a wide range of capacities, footprints, motor types and control options.


## Heat Exchangers



Wide Range of Custom Coils



High Pressure Stainless Steel Coils



Titanium Coils

## Dry & Adiabatic Units



**F Series**  
Air-Cooled Condenser or  
Fluid Cooler



**V-Energizer**  
CO<sub>2</sub> Evaporator



**V-Dry Cooler**  
Air-Cooled Condenser or  
Fluid Cooler Adiabatic Pads

# THERMAL ICE STORAGE SYSTEMS

## Environmentally Friendly Technology


Thermal ice storage provides many environmentally-friendly opportunities that are a result of reduced peak electrical demand. Ice storage shifts power demand to low-cost periods thereby reducing energy costs.



**ICE-PAK®**  
Ice-Chilled Energy Storage Units



**Ice Coils**



EVAPCO Ice Coils

## MicroChannel Heat Exchangers

Our brazed aluminum heat exchangers for the HVAC/R and Industrial Process markets use Advanced MicroChannel Technology. This innovative technology offers higher performance, smaller size and features and capabilities not found in traditional fin/tube heat exchangers.



**C Series**  
Condensers




**E & HP Series**  
Evaporator & Heat Pump



**F Series**  
Fluid & Chilled Water



**Replacement Coils**  
HVAC/R Equipment



**MicroCoil™ Series**  
Serpentine Coils

## Coil Technology



MicroChannel Extrusion




Controlled Atmosphere Brazing Furnace

# REPLACEMENT PARTS

EVAPCO is your best parts source for all evaporative and dry cooling equipment

## Any Part, Any Manufacturer, Any Time

Available parts include ...



... and many more

## MR. GOODTOWER® SERVICE CENTERS



Mr. GoodTower®

Specialists in the Restoration and Upgrade of All Types of Evaporative Cooling Equipment



Improve thermal performance with high efficiency fill




Improve safety and access with service platforms




Maintain operational integrity with new mechanical components


## Film Fills



**TechClean Fill**  
Offset Vertical Fluted  
High Efficiency  
Counterflow Film Fill



**Evap-Pak 1200/  
Opti-Pac 1200 Fill**  
The Highest Efficiency  
Film Fill Available for  
Counterflow Applications




**Opti-Pac 7500 Fill**  
Crossflow Fill Integrated Louver  
and Drift Eliminator  
(Bottom supported crossflow fill packs  
replace OEM Hanging Sheets)

## Wastewater Media



**Opti-Pac**  
**1200/1900/3000 & VF 30**  
Modules for Use in Wastewater Applications

## Splash Fills



**Opti-Bar**  
High Efficiency Bar Style Splash Fill



**ArchBar**  
Long Spanning, High  
Efficiency Bar Style Splash Fill



**Opti-Grid**  
High Efficiency Splash Fill Designed for  
Performance, Strength & Versatility

## Drift Eliminators




**DriAir 80**  
High Efficiency Cellular Drift Eliminator for  
Counterflow & Crossflow Applications




**DriAir 150**  
Cellular Drift Eliminator for  
Counterflow & Crossflow Applications

## FIBERGLASS PULTRUSIONS

Fiberglass materials provided exclusively to EvapTech and its subsidiaries



## Fans for Cooling Systems



**Super Low Sound Fan Series SLSF**



**Aluminum Fan Series**



**NCR/STEP Series Fan**  
Super High Efficiency

## Fans for Ventilation Systems



**Main Ventilation System TVA Series Fan**  
High Efficiency



**Road Way Ventilation System – FRP**  
High Temperature Class



**Secondary Ventilation System – TJF**  
High Efficiency

## Ventilation System for Special Applications



Wind Tunnel



Blades in Carbon Fiber and Kevlar for Ventilation of Electric Power Generators



Rotors for Wind Tunnel Wireless Controlled

# NORTH AMERICA LOCATIONS




**EVAPCO, Inc.**  
World Headquarters & Research Center  
Taneytown, Maryland



EVAPCO Key Building, Taneytown, Maryland



EvapTech, Inc., Edwardsville, Kansas



EVAPCO Dry Cooling, Bridgewater, New Jersey



EVAPCO Midwest, Greenup, Illinois



EVAPCO Alcoil, York, Pennsylvania



Evapcold Manufacturing, Greenup, Illinois



EVAPCO LMP, Laval, Quebec



Tower Components, Inc., Ramseur, North Carolina



EVAPCO Iowa, Lake View, Iowa



RVS Corporation, Bryan, Texas



EVAPCO West, Madera, California



EVAPCO SelectTech, Belmont Michigan

# INTERNATIONAL LOCATIONS



**EVAPCO Europe BV**  
European Headquarters  
Tongeren, Belgium



EVAPCO Brasil Equipamentos Industriais Ltda.,  
São Paulo, Brazil



EVAPCO Europe, S.r.l., Milano, Italy



EVAPCO Europe, S.r.l., Sondrio, Italy



FanTR, São Paulo, Brazil



EVAPCO S.A. (Pty.) Ltd., Isando, South Africa



Evap Egypt Engineering Industries Co., Cairo, Egypt



EVAPCO Europe A/S, Aabybro, Denmark



EVAPCO Air Cooling Systems (Jiaxing) Company,  
Ltd., Jiaxing, China



EVAPCO Australia (Pty.) Ltd., Riverstone, NSW  
Australia



EVAPCO (Beijing) Refrigeration Equipment Co.,  
Ltd, Beijing, China



**EVAPCO Asia Pacific  
Headquarters**  
Shanghai, China







World Headquarters  
 Research & Development Center  
 EVAPCO Manufacturing Facilities

## EVAPCO, Inc. — World Headquarters & Research / Development Center

P.O. Box 1300 • Westminister, MD 21158 USA  
 410.756.2600 • [marketing@evapco.com](mailto:marketing@evapco.com) • [evapco.com](http://evapco.com)

### North America

**EVAPCO, Inc.**  
**World Headquarters**  
 Westminister, MD USA  
 410.756.2600  
[marketing@evapco.com](mailto:marketing@evapco.com)

**EVAPCO East**  
 Taneytown, MD USA

**EVAPCO East**  
 Key Building  
 Taneytown, MD USA

**EVAPCO Midwest**  
 Greenup, IL USA  
 217.923.3431  
[evapcomw@evapcomw.com](mailto:evapcomw@evapcomw.com)

**Evapcold Manufacturing**  
 Greenup, IL USA

**EVAPCO West**  
 Madera, CA USA  
 559.673.2207  
[contact@evapcwest.com](mailto:contact@evapcwest.com)

**EVAPCO Alcoil, Inc.**  
 York, PA USA  
 717.347.7500  
[info@evapco-alcoil.com](mailto:info@evapco-alcoil.com)

**EVAPCO Iowa**  
 Lake View, IA USA

**EVAPCO Iowa**  
 Sales & Engineering  
 Medford, MN USA  
 507.446.8005  
[evapcomn@evapcomn.com](mailto:evapcomn@evapcomn.com)

**EVAPCO LMP ULC**  
 Laval, Quebec, Canada  
 450.629.9864  
[info@evapcolmp.ca](mailto:info@evapcolmp.ca)

**EVAPCO Select Technologies, Inc.**  
 Belmont, MI USA  
 844.785.9506  
[emarketing@evapcoselect.com](mailto:emarketing@evapcoselect.com)

**Refrigeration Vessels & Systems Corporation**  
 Bryan, TX USA  
 979.778.0095  
[rvs@rvscorp.com](mailto:rvs@rvscorp.com)

**Tower Components, Inc.**  
 Ramseur, NC USA  
 336.824.2102  
[mail@towercomponentsinc.com](mailto:mail@towercomponentsinc.com)

**EvapTech, Inc.**  
 Edwardsville, KS USA  
 913.322.5165  
[marketing@evaptech.com](mailto:marketing@evaptech.com)

**EVAPCO Dry Cooling, Inc.**  
 Bridgewater, NJ USA  
 908.379.2665  
[info@evapcodc.com](mailto:info@evapcodc.com)

**EVAPCO Dry Cooling, Inc.**  
 Littleton, CO USA  
 908.895.3236  
[info@evapcodc.com](mailto:info@evapcodc.com)

### Asia Pacific

**EVAPCO Asia Pacific Headquarters**  
 Baoshan Industrial Zone Shanghai, P.R. China  
 (86) 21.6687.7786  
[marketing@evapcochina.com](mailto:marketing@evapcochina.com)

**EVAPCO (Shanghai) Refrigeration Equipment Co., Ltd.**  
 Baoshan Industrial Zone, Shanghai, P.R. China

**EVAPCO (Beijing) Refrigeration Equipment Co., Ltd.**  
 Huairou District, Beijing, P.R. China  
 (86) 10.6166.7238  
[marketing@evapcochina.com](mailto:marketing@evapcochina.com)

**EVAPCO Air Cooling Systems (Jiaxing) Company, Ltd.**  
 Jiaxing, Zhejiang P.R. China  
 (86) 573.8311.9379  
[info@evapcochina.com](mailto:info@evapcochina.com)

**EVAPCO Australia (Pty.) Ltd.**  
 Riverstone, NSW, Australia  
 (61) 02.9627.3322  
[sales@evapco.com.au](mailto:sales@evapco.com.au)

**EvapTech (Shanghai) Cooling Tower Co., Ltd**  
 Baoshan District, Shanghai, P.R. China.  
 Tel: (86) 21.6478.0265

**EvapTech Asia Pacific Sdn. Bhd.**  
 Puchong, Selangor, Malaysia  
 (60) 3.8070.7255  
[marketing-ap@evaptech.com](mailto:marketing-ap@evaptech.com)

### Europe | Middle East | Africa

**EVAPCO Europe EMENA Headquarters**  
 Tongeren, Belgium  
 (32) 12.39.50.29  
[evapco.europe@evapco.be](mailto:evapco.europe@evapco.be)

**EVAPCO Europe BV**  
 Tongeren, Belgium

**EVAPCO Europe, S.r.l.**  
 Milan, Italy  
 (39) 02.939.9041  
[evapcoeuropa@evapco.it](mailto:evapcoeuropa@evapco.it)

**EVAPCO Europe, S.r.l.**  
 Sondrio, Italy

**EVAPCO Europe A/S**  
 Aabybro, Denmark  
 (45) 9824.4999  
[info@evapco.dk](mailto:info@evapco.dk)

**EVAPCO Europe GmbH**  
 Meerbusch, Germany  
 (49) 2159.69560  
[info@evapco.de](mailto:info@evapco.de)

**EVAPCO Middle East DMCC**  
 Dubai, United Arab Emirates  
 (971) 56.991.6584  
[info@evapco.ae](mailto:info@evapco.ae)

**Evap Egypt Engineering Industries Co.**  
*A licensed manufacturer of EVAPCO, Inc.*  
 Nasr City, Cairo, Egypt  
 (20) 10.054.32.198  
[evapco@tiba-group.com](mailto:evapco@tiba-group.com)

**EVAPCO S.A. (Pty.) Ltd.**  
*A licensed manufacturer of EVAPCO, Inc.*  
 Isando, South Africa  
 (27) 11.392.6630  
[evapco@evapco.co.za](mailto:evapco@evapco.co.za)

### South America

**EVAPCO Brasil**  
 Equipamentos Industriais Ltda.  
 Indaiatuba, São Paulo, Brazil  
 (55) 11.5681.2000  
[vendas@evapco.com.br](mailto:vendas@evapco.com.br)

**FanTR Technology Resources**  
 Itu, São Paulo, Brazil  
 (55) 11.4025.1670  
[fantr@fantr.com](mailto:fantr@fantr.com)